



Eight rear outlets, lighted switch, 15A. Receptacles rotated 90 degrees and 4 outlets spaced to accommodate transformers. 15' (4.6m) cord. Perma Power computer grade surge protection.

## Features & Benefits

Eight rear outlets, lighted switch, 15A. Receptacles rotated 90 degrees and 4 outlets spaced to accommodate transformers. 15' (4.6m) cord. Perma Power computer grade surge protection.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776012217
Country Of Origin	China	Application Sector	Commercial, Residential
Standard	cULus Recognized: File E66421: Guide XBYS2, XUHT2, VZCA13	Type	PIOC

### Dimensions

Product Width US	19.0 in	Product Weight US	3.1 lb
Product Height US	2.57 in	Product Length US	1.75 in

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Additional Information

RoHS Compliant	Yes
----------------	-----

### Technical Information

Phase	Single Stage	Connection	Cord-ended
Class	75	Amperage	15 A
Short Circuit Rating	36000 Amps [12000 Amps L-N 12000 Amps L-G 12000 Amps N-G]	Response Time	<1 ns
Mounting Type	Rack Mounting	Mounting	Yes
Type of Indicators	Light	Voltage	120.0 V