



Wiremold
FLUSH POKE-THRU ASSY/20ABK/TC/LJB
Part No. RC3ATCBK-LJB



Flush Style AV3 Poke-Thru Devices are an excellent solution for bringing communication and A/V services to the workstation in an open space, above-grade floor environment. All Wiremold Flush Style Poke-Thru Devices come with built-in TopGuard™ protection, an industry-leading design that meets and exceeds UL scrub water exclusion requirements for tile and carpet floors. Topguard protection prevents water, dirt, or debris from entering not just the power devices, but also the communication devices. All Wiremold Flush Style Poke-Thru Devices can be installed on tile, carpet, or wood covered floors. Each of these devices provides an excellent solution for both new or retrofit construction, with typical applications that include office buildings, airports, malls, shopping centers, libraries, and schools.

Features & Benefits

A/V device includes one prewired 20A duplex receptacle which can be wired as a standard receptacle or isolated ground

Includes one Extron bezel to accept Extron MAAP mini architectural adapter plates

(Extron devices sold separately, only through authorized Extron dealers)

Includes Ortronics® TracJack and Series II mounting adapters and Wiremold Open System adapters and inserts

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786564151210	Country Of Origin	Mexico
Construction	Assembled	Application Sector	Commercial, Education, Healthcare, Hospitality
Standard	UL Fire Classified, cULus, NEC	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Poke-Thru		

Dimensions

Product Weight US	3.96 lb	Core Hole Size	4 in
-------------------	---------	----------------	------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Floor Type	Carpet, Tile	Is Pre-Wired	Yes
------------	--------------	--------------	-----

Service Capacity	Dual	Fire Rating	2 hr
------------------	------	-------------	------

Cable Entry	1/2 in	Number of Outlets	2
-------------	--------	-------------------	---
