



Assembled unit. Prewired 20A duplex receptacle can be wired as a standard duplex receptacle or isolated ground. Flange available in painted gray (GY), black (BK), ivory (VY) or brushed metal finishes in aluminum (AL), and brass (BS). Slide covers match the painted flange colors: gray, black, and ivory. Aluminum and brass flanges shipped with black slide cover. Brass flange also available with nonmetallic brass colored slide holder (AB). Aluminum flange also available with nonmetallic aluminum colored slide holder (AA). Includes Wiremold Open System unloaded adapters to accept four discrete keystone connectors from most manufacturers. Unit also includes two Ortronics TracJack adapters and two Ortronics Series II adapters. Modular jacks sold separately. NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. RC3 Series Poke-Thru Devices require a 4" (102mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8" minimum.

Features & Benefits

Assembled unit Prewired 20A duplex receptacle can be wired as a standard duplex receptacle or isolated ground	Flange available in painted gray (GY), black (BK), ivory (VY) or brushed metal finishes in aluminum (AL), and brass (BS)
Slide covers match the painted flange colors: gray, black, and ivory	Aluminum and brass flanges shipped with black slide cover
Brass flange also available with nonmetallic brass colored slide holder (AB)	Includes Wiremold Open System unloaded adapters to accept four discrete keystone connectors from most manufacturers
Includes Wiremold Open System unloaded adapters to accept four discrete keystone connectors from most manufacturers	Unit also includes two Ortronics TracJack adapters and two Ortronics Series II adapters
Modular jacks sold separately	NOTE: Assembled with scrub water gasket
For use on tile or carpet floors	Modular jacks sold separately
Not designed to work with bare concrete or terrazzo	Floor covering thickness 1/8" minimum

Specifications

General Info

Product Line	Wiremold	UPC Number	786564067061
Country Of Origin	Mexico	Construction	Assembled
Number of Knockouts	2	Application Sector	Commercial, Education, Healthcare, Hospitality

Standard	UL Fire Classified, cULus, NEC	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
----------	--------------------------------	---------------	--

Type	Poke-Thru
------	-----------

Dimensions

Product Width US	7.5 in	Product Weight US	7.407 lb
------------------	--------	-------------------	----------

Product Height US	16.0 in	Cubic Capacity	24.5 in ³
-------------------	---------	----------------	----------------------

Core Hole Size	4 in
----------------	------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Floor Type	Carpet, Tile	Is Pre-Wired	Yes
------------	--------------	--------------	-----

Service Capacity	Dual	Fire Rating	2 hr
------------------	------	-------------	------

Amperage	20 A	Cable Entry	knockout
----------	------	-------------	----------

Number of Outlets	2
-------------------	---
