



Complete with combination 1 1/4" and 2" trade size threaded conduit openings and closure plugs. Must be used with a conduit connector (not included) at the adapter assembly plate to maintain fire classification. Finish flange/cover assembly available in gray (GY), black (BK), and brushed aluminum (AL). NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. RC9AM2TC Series Poke-Thru Devices require a 3" (76mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8" minimum.

Features & Benefits

Complete with combination 1 1/4" and 2" trade size threaded conduit openings and closure plugs

Must be used with a conduit connector (not included) at the adapter assembly plate to maintain fire classification

Finish flange/cover assembly available in gray (GY), black (BK), and brushed aluminum (AL)

NOTE: Assembled with scrub water gasket

For use on tile or carpet floors

Not designed to work with bare concrete or terrazzo

Not designed to work with bare concrete or terrazzo

Floor covering thickness 1/8" minimum

Specifications

General Info

Product Line	Wiremold	UPC Number	786564024767
Country Of Origin	Mexico	Construction	Assembled
Cover Style	Furniture Feed	Number of Knockouts	1
Application Sector	Commercial, Education, Healthcare, Hospitality	Standard	UL Fire Classified, cULus, NEC
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Poke-Thru

Dimensions

Product Weight US	3.5 lb	Core Hole Size	3 in
-------------------	--------	----------------	------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Floor Type	Carpet, Tile	Service Capacity	Dual
------------	--------------	------------------	------

Fire Rating	2 hr	Cable Entry	CONDUIT
-------------	------	-------------	---------
