



radiant Collection
radiant® Two Single-Pole Switches, Black
Part No. RCD11BKCC6



Control two separate lights or devices from a single location with this combination switch. Designed to emulate the sleek lines of the collection's paddle switches, it delivers flexible, space-saving control with the sophisticated look of radiant. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Offers installation flexibility with space-saving style, as part of the extensive offering from the radiant® Collection.

Features durable, high-impact resistant thermoplastic construction.

Designed to install easily with a narrower back body and captivated mounting screws.

Patented Snap-In Light Module (sold separately) transforms a combination switch into an illuminated switch in seconds.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007054835
Country Of Origin	China	Features	Combination, Locator Light
Switch Type	Push	Number of Switches	2
Application Sector	Residential	Warranty Type	1-Year Limited Warranty
Type	Switch		

Dimensions

Product Width US	1.29 in	Product Depth US	1.59 in
------------------	---------	------------------	---------

Product Height US 3.81 in

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Contact Rating	15 Amp, 120/125 VAC	Number of Gangs	1
----------------	---------------------	-----------------	---

Amperage	15 A	Number of Poles	Single Pole
----------	------	-----------------	-------------

Wire Size	#14 - #10 AWG	Mounting Type	Box
-----------	---------------	---------------	-----

Voltage	120.0 V
---------	---------
