




radiant Collection  
radiant® Single Pole/3-Way Switch with 15A Tamper-Resistant Outlet, White  
Part No. RCD38TRW



A step up from ordinary, this combination switch and outlet from the radiant® Collection provides convenience and flexibility, as well as style. Operable in both single-pole and 3-way applications, you can use it alone to control one light or fixture, or use with another 3-Way switch for controlling the light from two locations. Also includes a tamper-resistant outlet for safe access to the basic power every home needs. Part of the radiant® Collection, it features clean lines and a smooth finish for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Replaces a standard switch/outlet with ease, in as little as 10 minutes.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style.

Offers installation flexibility, working in both single-pole and 3-way applications.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007055085
Country Of Origin	China	Number of Receptacles	1
Features	Combination, Locator Light	Switch Type	Push
Number of Switches	1	Outlet Type	Tamper-Resistant
Application Sector	Residential	Standard	cULus, UL Listed
Warranty Type	1-Year Limited Warranty	Type	Outlet, Switch

### Dimensions

---

Product Width US	1.29 in	Product Depth US	1.59 in
------------------	---------	------------------	---------

---

Product Height US	3.81 in
-------------------	---------

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Technical Information

---

Is Tamper-Resistant	Yes	Operating Cycles	50000
---------------------	-----	------------------	-------

---

Contact Rating	15 Amp, 120/125 VAC	Number of Gangs	1
----------------	---------------------	-----------------	---

---

Amperage	15 A	Number of Poles	3-Way, Single Pole
----------	------	-----------------	--------------------

---

Wire Size	#14 - #10 AWG	Indoor/Outdoor	Indoor
-----------	---------------	----------------	--------

---

Mounting Type	Box	Voltage	120.0 V
---------------	-----	---------	---------

---

Environmental Conditions	Flammability Rating: UL 94 V2
--------------------------	-------------------------------

---