Ortronics

28awg Reduced diameter C6A/10G channel cord Orange 3FT

Part No. RDC61003-03

The RDC610 series of modular patch cords offer the reduced diameter of four pairs of 28AWG conductors, providing CAT6A channel performance for high density applications, when looking to reduce congestion or improve airflow through cabling pathways. Common applications include high-density cabling areas such as data centers, end-of-row (EoR) and top-of-rack (ToR) installations or areas such as telecom rooms and equipment rooms.

Features & Benefits

Each cord is 100% factory tested: Ensures every cord shipped support Category 6a channel specifications.

Reduced cable diameter: Tighter bend radiuses & occupy less cable management space supporting more airflow

Premium plug designed for reduced OD 28AWG patch cable: Protects performance through the plug termination

Snagless plug design: Protects plugs when routing through cable managers or pathways.

Premium 28AWG conductor cordage: Reliable performance and durable cord life.

Backwards compatible to Category 6, and 5e: Supports lower category installations and components.

Improved cable flexibility: Supports simple routing and cable management

Specifications

General Info

Product Line	Ortronics	UPC Number	662875996439
Country Of Origin	Mexico	Type	Reduced Diameter Patch Cords

Dimensions

Product Length US	3.0 FT

Additional Information

Product Environmental Profile	Yes