



Features & Benefits

For use with incandescent bulbs and fixtures on typical residential (and light commercial) wiring. Usable in both single-pole and 3-way applications. Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark. Constant memory features returns lights to their previous level after a power failure or outage.

Features durable, high-impact resistant thermoplastic construction. More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection. Screw pressure plate back wire allows easier installation and fit into the wall box

Eliminates the need to derate LED bulbs when in multi-gang situations For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	RHCL453PNICCV4
Color	Nickel	Finish	Metallic
UPC Number	785007053739	Country Of Origin	China
Switch Type	Paddle	Number of Switches	1
Application Sector	Residential	Warranty Type	Limited Lifetime Warranty

Type Dimmer

Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		

Technical Information

Number of Gangs	1	Amperage	15 A
Bulb Compatibility	Incandescent	Number of Poles	3-Way, Single Pole
Wire Size	#14 - #10 AWG	Wattage	700 W
Mounting Type	Box	Supply Voltage	120 VAC
Voltage	120.0 V		
