



radiant Collection  
radiant® Incandescent 700W Dimmer, White  
Part No. RH703PW



Upgrade your space with precise dimming control and exceptional style. This dimmer from the radiant® Collection is optimized for use with incandescent bulbs and fixtures. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

For use with incandescent bulbs and fixtures on typical residential (and light commercial) wiring. Usable in both single-pole and 3-way applications. Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark. Constant memory features returns lights to their previous level after a power failure or outage.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Screw pressure plate back wire allows easier installation and fit into the wall box

Eliminates the need to derate LED bulbs when in multi-gang situations

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007053401
Country Of Origin	China	Features	Color Change Kit, Locator Light, Low-End Trim (Dim Range)
Switch Type	Paddle, Single Pole 3-Way, Slider	Number of Switches	1
Application Sector	Residential	Standard	cULus, CSA Listed, UL 1472

---

Warranty Type	Limited Lifetime Warranty	Type	Dimmer
---------------	---------------------------	------	--------

---

### Dimensions

---

Product Width US	1.75 in	Product Depth US	1.25 in
------------------	---------	------------------	---------

---

Product Height US	4.25 in
-------------------	---------

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Technical Information

---

Load Rating	120V 700W (Halogen), 120V 700W (Incandescent)	Dimming Compatibility	Forward Phase
-------------	---	-----------------------	---------------

---

Frequency Rating	60 Hz	Number of Poles	Single Pole 3-Way
------------------	-------	-----------------	-------------------

---

Wire Size	#14 - #10 AWG	Requires Neutral Wire	No
-----------	---------------	-----------------------	----

---

Indoor/Outdoor	Indoor	Mounting Type	Wall Box
----------------	--------	---------------	----------

---

Wire Connection Type	Screw Terminals	Voltage	120 VAC
----------------------	-----------------	---------	---------

---

Load Type	Halogen, Incandescent	Environmental Conditions	95% (relative humidity, non-condensing)
-----------	-----------------------	--------------------------	---

---