radiant Collection

radiant® LED/CFL Dimmer, White

Part No. RHL743PW



Upgrade your space with precise dimming control and exceptional style. This dimmer from the radiant® Collection is optimized for use with LED bulbs and fixtures compliant with the SSL 7A standard for energy efficiency. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

SSL 7A - Compliant, this dimmer is for use with LED bulbs and fixtures also designed to the SSL 7A standard for efficiency. For use in both single-pole and 3-way applications.

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

Constant memory features returns lights to their previous level after a power failure or outage.

No derating* required for 2-gang applications. * Reducing the maximum wattage a dimmer can handle. This is sometimes required for multi-gang applications.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	China
Features	Locator Light	Switch Type	Paddle, Slider
Number of Switches	1	Application Sector	Residential
Standard	CSA Listed, cULus, UL Listed	Warranty Type	Limited Lifetime Warranty
Type	Dimmer		

Dimensions

Product Width US	1.29 in	Product Depth US	1.0 in
Product Height US	3.18 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Number of Gangs	1	Amperage	5.5 A
Bulb Compatibility	CFL, Halogen, Incandescent, LED	Number of Poles	3-Way, Single Pole
Wattage	700 W	Mounting Type	Box
Voltage	120 V	Load	LED, CFL, Incandescent
Environmental Conditions	Humidity: Less than 95% non condensing		