



radiant Collection
Discontinued - radiant® Single Pole 3-Way Vacancy Sensor, Tri-Color
Part No. RRW600VTCCCV4



Never worry about leaving the lights on, with the radiant® Vacancy Sensor. It automatically shuts off when a room is empty, and includes an adjustable delay setting of up to 30 minutes to match your needs. Designed for ease and style, it features a built-in locator light, and the sleek, clean lines of radiant® for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

- Passive infrared (PIR) sensor switch technology with 180° coverage up to 600 sq. ft. Rated for up to 600W (5A) of LED lighting.
 - Turn the light on when you enter, and let it turn itself off automatically after you leave for true convenience. Perfect for bathrooms, hallways, closets, garages, and more.
 - Features an adjustable time delay to off after no motion is detected. Delay settings range from 30 seconds to 20 minutes after the room is vacated (default 20 minute delay).
 - Replace any basic light or fan switch in 15 minutes or less. Supports single pole and multi-location installs. No neutral required.
 - More color options available to fit any style, including finishes to match current hardware and lighting trends.
- Works with virtually any bulb/fixture, including: LED, incandescent, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp.
 - Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.
 - Manual ON/Auto OFF functionality. Meets California Title 24 requirements for automatic off lighting control.
 - Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007496581
Country Of Origin	China	Features	Adjustable Time Delay, Motion Sensor
Switch Type	Motion Sensor, sofTap	Installation Location	Wall Box

Application Sector	Hospitality, Light Commercial, Multi-Dwelling Unit, Residential	Warranty Type	Limited Lifetime Warranty
Technical Information			
Load Rating	120V 5A (ELV), 120V 5A 600W (CFL), 120V 5A 600W (LED), 120V 600VA (Fluorescent), 120V 600VA (MLV), 120V 600W (Halogen), 120V 600W (Incandescent)	Horsepower Rating	1/6 HP @ 120 VAC
Sensor Coverage Pattern	180 deg	Sensor Type	Vacancy
Timer Duration	20 Minutes, 30 Seconds-20 Minutes	Number of Poles	Multi-Location, Single Pole 3 Way
Wire Size	#14 - #10 AWG	Input Voltage	120 VAC
Requires Neutral Wire	No	Line Frequency	60 Hz
Indoor/Outdoor	Indoor	Sensor Coverage	600 sq ft
Mounting Type	Wall Box	On Function	Manual On
Operating Humidity	0-95% RH (Non-Condensing)	Sensing Range	Major Motion 35 ft, Minor Motion 20 ft
Wire Connection Type	Flying Leads	Voltage	120 VAC
Load Type	CFL, Fan Motor, Halogen, Incandescent:Fluorescent, LED		