



Pass and Seymour
Replacement Switch with Auxiliary Contact, 60A
Part No. RS60AX

60As Replacement Switch with Auxiliary Contact



Specifications

General Info

Product Line	Pass & Seymour	Color	Blue
Finish	Matte	UPC Number	785007133820
Country Of Origin	United States	Application Sector	Industrial
Type	Replacement Switch		

Dimensions

Product Width US	8.3 in	Product Depth US	7.1 in
Product Height US	14.03 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Horsepower Rating	15 HP @ 3ø 240 VAC, 15 HP @ 480 VAC, 15 HP @ 600 VAC, 3 HP @ 120 VAC, 30 HP @ 3ø 480 VAC, 30 HP @ 3ø 600 VAC, 7-1/2 HP @ 240 VAC, 7-1/2 HP @ 277 VAC	Connection	Hardwired
Amperage	60 A	Enclosure Type	Not included.

Wire Size

#14 - #10 AWG

Maximum Horsepower Rating

30 HP @ 3Ø
600VAC

Voltage

120 to 600 V
