



radiant Collection
radiant® 20A Wave® Switch
Part No. RSWW203



When it comes to lighting control, it's time to keep your hands...or at least their messes...to yourself. Thanks to Legrand's innovative touchless technology, this sleek switch lets you turn lights on or off with a simple wave for the germ-and-worry solution that's perfect for any home's entryway or kitchen, as well as for shared spaces like offices, hotels and more. Wave "hello" to cleaner, more convenient control for cleaner, more convenient spaces. Made exclusively for use with the screwless Wall Plates from the radiant® Collection, sold separately. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Features innovative touchless control for a convenient, germ-free way to turn on lights...all it takes is a simple wave

Installs easily in 15 minutes or less, fitting into an existing electrical box. Usable in both single-pole and 3-way applications

Made for use in both residential and commercial applications; features durable construction to withstand rigorous cleaning practices

Includes a rating of up to 3/4 HP for adding touchless control to small motors

Adjust the internal sensor to respond to movement from 1 to 6 inches from the switch face to fit your space and needs

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007382518
Country Of Origin	China	Switch Type	Wave
Application Sector	Residential	Warranty Type	1-Year
Type	Decorator, Switch		

Dimensions

Product Width US	1.72 in	Product Depth US	1.03 in
------------------	---------	------------------	---------

Product Height US	4.2 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Seismic Tested	No	Amperage	20 A
----------------	----	----------	------

Number of Poles	3-Way, Single Pole	Wire Size	#14 - #10 AWG
-----------------	--------------------	-----------	---------------

Indoor/Outdoor	Indoor	Connection Type	Internal Pressure Plates
----------------	--------	-----------------	--------------------------
