



The RT-100 Programmable Countdown Time Switch automatically turns lighting or other loads off when the programmed on-time expires. It replaces standard single-pole wall switches for energy savings inside and outside.

Features & Benefits

Collection consolidated to white option	Programmable switch for automatic-off control
Oversize silver alloy contacts for long life and better heat dissipation.	Backlit display shows countdown in progress
Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.	Lighted switch for visibility in darkened rooms
Fiber terminal insulation barriers standard. Ideal for garages, outdoor lighting, storage areas and spa control	
Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.	Programmable on-time from 5 minutes to 12 hours
Bodies, covers, and toggles molded of durable nylon.	Single Pole-Double Throw and Double Pole-Double Throw.
Locking Switches supplied with one 1498-NT key.	Normally open.
For covering patents, see www.legrand.us/patents .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .

Specifications

General Info

Product Line	Wattstopper	Replaced by Part Number	RT-100-W
Color	Ivory	UPC Number	754182918362
Country Of Origin	China	Features	Locator Light, Timer
Switch Type	Push	Application Sector	Commercial

Warranty Type	5-Year
---------------	--------

Dimensions

Product Width US	1.8 in	Product Weight US	0.2985 lb
------------------	--------	-------------------	-----------

Product Volume US	13.3 cu in	Product Depth US	1.8 in
-------------------	------------	------------------	--------

Product Height US	4.1 in
-------------------	--------

Additional Information

RoHS Compliant	Yes	DesignLights Consortium Qualified System	Yes
----------------	-----	--	-----

Security	Yes
----------	-----

Technical Information

Number of Buttons	1	Amperage	5 A
-------------------	---	----------	-----

Timing Range	5-55 minutes (five-minute increments) to 1-12 hours (15-minute increments)	Wattage	600 W
--------------	--	---------	-------

Connection Type	Wired
-----------------	-------
