



Pass and Seymour  
Non-NEMA 3 Wire Plug - Black Back, White Front Body  
Part No. S2348DF

Non-Nema Plug, 14amp 125-480V, IP20 Suitability Back Front Body



## Features & Benefits

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.

Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

Raised ribs provide non-slip gripping profile for turning to lock and unlock.

Double dovetail design provides superior protection against cord pull-out forces.

Impact- and corrosion-resistant durable nylon 6/6 shell material.

Rounded back contour reduces snags and hang-ups on the job site.

Scalloped shell design provides non-slip gripping surface for insertion and withdrawal.

Visible stamped NEMA configuration and device rating.

New-design external cord grips provide visible assurance of safe and proper cord retention.

Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007659757	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL 498

### Dimensions

Product Width US	1.406 in	Product Length US	1.8 in
------------------	----------	-------------------	--------

### Technical Information

---

Phase

Three

Number of Wires

3

---

Amperage

15 A

Number of Poles

Double Pole

---

Wire Size

18 - 0 AWG

---