



Pass and Seymour
Screw Mount Steel Stud Box with Quick/Click
Part No. S235RACSMH



Double Gang Screw Mount Steel Stud Box with captive Combo Head Self-Tapping Mount Screws on Each End. Four Auto/Clamps on Each End, 3-inch Depth for manufacture housing walls. 100 pack.

Features & Benefits

Available in single, single deep, two, three and four gang, and 4 inch round ceiling boxes.

Single gang include Quick/Entry feature.

Screws have combination Hex/Phillips washer heads.

Can be used for steel, aluminum, or wood studs.

Locator ribs ensure proper alignment on stud and proper offset depth.

All multi-gang and ceiling boxes include exclusive Auto/Clamp feature.

Specially designed drill point rapidly penetrates medium gauge steel studs.

Quick/Click feature on wall boxes offers fast and dependable installation of devices.

Molded of high-impact thermoplastic.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007269864	Country Of Origin	United States
Construction	Steel	Application Sector	Commercial, Residential
Standard	UL Listed		

Dimensions

Cubic Capacity	18 in ³
----------------	--------------------

Additional Information

Product Environmental Profile Yes

Technical Information

Number of Outlets 2
