



Tamper-Resistant Clock Hanger Recessed Receptacle with Smooth Wall Plate 15A, 125V. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Single recessed receptacle. Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007197587	Country Of Origin	Mexico
Number of Receptacles	1	Outlet Type	Tamper-Resistant
Application Sector	Commercial, Residential	Standard	UL 498
Type	Outlet		

Dimensions

Product Width US	2.74 in	Product Depth US	1.88 in
Product Height US	4.478 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole

Wire Size

14 - 12 AWG

Indoor/Outdoor

Indoor
