



Tamper-Resistant Clock Hanger Recessed Receptacle with Smooth Wall Plate 15A, 125V. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Single recessed receptacle.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates; and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007180169
Country Of Origin	Mexico	Number of Receptacles	1
Outlet Type	Tamper-Resistant	Application Sector	Commercial, Residential
Standard	UL 498	Type	Outlet

### Dimensions

Product Width US	2.74 in	Product Depth US	1.88 in
Product Height US	4.478 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor		