

Cisco SFP-10G-BXU-I Compatible 10GBase-BX SFP+ Transceiver (SMF, Tx: 1270nm Rx: 1330nm, 10-20km, LC Duplex, DDM, I-Temp)



Features & Benefits

Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.

99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.

98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.

Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

Specifications

General Info

| | | | |
|-------------------|-------------|---------------|--------------|
| Product Line | Ortronics | UPC Number | 662875078548 |
| Country Of Origin | China | Warranty Type | Lifetime |
| Type | Transceiver | | |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 13.7 mm | Product Depth US | 56.6 mm |
| Product Height US | 12.8 mm | | |

Technical Information

| | | | |
|---------------------------|-------------|---------------------------|-----------|
| Fiber Optic Cable Type | Single-Mode | Max Distance Support | 20 km |
| Operating Temperature Min | -40 °C | Operating Temperature Max | 85 °C |
| Data Transfer Rate | 10 Gbps | Connector Type | LC Duplex |
| Form Factor | SFP+ | | |