



Pass and Seymour  
**1-Gang 430 Stainless Steel Wall Plate, 0.53-in Round Opening for Telephone or Cable**  
Part No. SL12



Single-Gang, Single telephone or cable outlet removable 13/32 in ID grommet in 17/32-inch fthole. Strap mounted with adjustable yoke. One #340 yoke. 430 Stainless steel.

## Features & Benefits

Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.

Packaged in protective film, with finish-matching screws.

Paintable to match plastic plates.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Variety of special plated finishes.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Stainless Steel
Finish	Metallic	UPC Number	785007658088
Country Of Origin	United States	Wall Plate Size	Standard Size
Wall Plate Type	Coaxial, Round, Telephone	Application Sector	Commercial, Residential
Warranty Type	1-Year Limited Warranty	Type	Wall Plate

### Dimensions

Product Width US	2.75 in	Product Depth US	0.2 in
Product Height US	4.5 in	Circular Outlet Diameter	0.53 mm

---

## Listing Agencies / 3rd Party Agencies

---

CSA Listed	Yes	cULus ListingNumber	143223
cULus Listed	Yes	CSA File Number	17695

---

## Additional Information

---

Product Environmental Profile Yes

---

## Technical Information

---

Thickness	0.032 in	Number of Gangs	1
Indoor/Outdoor	Indoor	Mounting Type	Strap Mounted
Orientation	Vertical		

---