



Pass and Seymour  
Combination Openings, 1 Toggle Switch and 1 Decorator, Two Gang, Ivory  
Part No. SP126I




Plate Plastic 2-Gang Toggle and Sierraplex Without Line

## Features & Benefits

Molded of non-combustible mar-proof material.

Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes.

Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.

Individually wrapped with color-matching screws.

Resistant to discoloration, grease, oil, solvent, and moisture.

Nominal thickness, .070 inch.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007681468
Country Of Origin	Mexico	Features	Combination
Wall Plate Type	Combination, Decorator, Toggle Switch	Application Sector	Commercial, Residential
Standard	CSA, UL514	Warranty Type	Limited Lifetime Warranty
Type	Wall Plate		

### Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
Product Height US	4.5 in		

---

## Listing Agencies / 3rd Party Agencies

---

CSA Listed	Yes	CSA File Number	17695
------------	-----	-----------------	-------

---

## Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

## Technical Information

---

Cutout	Toggle and Decorator	Thickness	0.07 in
--------	----------------------	-----------	---------

---

Number of Gangs	2	Wire Size	#14 - #10 AWG
-----------------	---	-----------	---------------

---

Indoor/Outdoor	Indoor	Mounting Type	Exposed Screws
----------------	--------	---------------	----------------

---

Orientation	Horizontal
-------------	------------

---