



Pass and Seymour
2-Gang Thermoset Wall Plate, 3 Blank, 1 Duplex Receptacle, Ivory
Part No. SP138I



Combination Wall Plate, 1 Blank and 1 Duplex Receptacle, 2-Gang

Features & Benefits

| | |
|---|--|
| Molded of non-combustible mar-proof material. | Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes. |
| Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond. | Individually wrapped with color-matching screws. |
| Resistant to discoloration, grease, oil, solvent, and moisture. | Nominal thickness, .070 inch. |

Specifications

General Info

| | | | |
|--------------------|-------------------------|-----------------|---------------------------------------|
| Product Line | Pass & Seymour | Color | Ivory |
| Finish | Matte | UPC Number | 785007188042 |
| Country Of Origin | Mexico | Construction | Plastic |
| Wall Plate Size | Standard Size | Wall Plate Type | Blank, Combination, Duplex Receptacle |
| Application Sector | Commercial, Residential | Standard | CSA, UL514 |
| Warranty Type | 1-Year Limited Warranty | Type | Wall Plate |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 4.56 in | Product Depth US | 0.2 in |
| Product Height US | 4.5 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|-----------------|-------|
| CSA Listed | Yes | CSA File Number | 17695 |
|------------|-----|-----------------|-------|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|-----------|---------|-----------------|---|
| Thickness | 0.07 in | Number of Gangs | 2 |
|-----------|---------|-----------------|---|

| | | | |
|----------------|--------|---------------|-------------|
| Indoor/Outdoor | Indoor | Mounting Type | Box Mounted |
|----------------|--------|---------------|-------------|

| | |
|-------------|----------|
| Orientation | Vertical |
|-------------|----------|
