



Pass and Seymour
2-Gang Thermoset Wall Plate, Two 0.625-in Round Opening for Telephone or Cable, Ivory
Part No. SP21I



Double gang, Double telephone or cable outlet 13/32-inch hole. Box mounted. Smooth Thermoset. .

Features & Benefits

Molded of rugged, practically indestructible Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: self-extinguishing nylon. ('TP' series only.) and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

Nominal thickness, .070 inch.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007186543
Country Of Origin	Mexico	Construction	Plastic
Wall Plate Size	Standard Size	Wall Plate Type	Outlet, Round
Application Sector	Commercial, Residential	Standard	CSA, UL514
Warranty Type	1-Year Limited Warranty	Type	Wall Plate

Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
Product Height US	4.5 in	Circular Outlet Diameter	0.625 mm

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	17695
------------	-----	-----------------	-------

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Thickness	0.07 in	Number of Gangs	2
Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
Orientation	Vertical		
