



Ortronics
Category 6A TechChoice Flat Patch Panel 48 Port 2RU Black
Part No. SP6AU48



TechChoice Cat6A/10G 48-port patch panel with multiport modules (6 jacks in a group) with supplied rear cable management. Circuit isolation and supports the alien crosstalk requirements of IEEE 10G and TIA Category 6a cabling specifications. Panel occupies two rack units.

Features & Benefits

- Tested and qualified to TIA 568-C Cat6A with SPC6A: More transparent mated union resulting in superior performance.
- Cat6A/10 Gig compatible IDC towers: Designed to accept larger Cat6A cable conductors.
- High density design: Maximizes rack utilization.
- Universally wired: 10 termination: Supports T568A and T568B installs.
- Supplied rear cable management: Supports good cabling practices.

Specifications

General Info

Product Line	Ortronics	Color	Black
UPC Number	662875996798	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	TIA-568.2-D, UL 1863, IEEE 802.3af / 802.3at and 802.3bt Type 3 and Type 4, FCC part 68 Subpart F, IEC-603-7 compliant
Warranty Type	5-Year	Type	Panel

Dimensions

Product Width US	19.0 in	Product Depth US	6.09 in
Product Height US	3.5 in		

Additional Information

RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
----------------	-----	---	-----

Technical Information

Category Performance Rating	Cat6a	Compatibility	TechChoice Keystone
Rack Units	2	Wire Gauge	22 AWG
Number of Ports	48	Shielded/Unshielded	Unshielded
Connector Type	RJ-45	Wattage	100 W
Voltage	60.0 V		
