



Pass and Seymour
2-Gang Thermoset Wall Plate, 1 Duplex Receptacle, 1 Decorator, Gray
Part No. SP826GRY



This 2-gang wall plate provides openings for 1-duplex receptacle and 1-Decorator device

Features & Benefits

| | |
|---|---|
| Molded of non-combustible mar-proof material. | Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates. |
| Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond. | Individually wrapped with color-matching screws. |
| Resistant to discoloration, grease, oil, solvent, and moisture. | Nominal thickness, .070 inch. |

Specifications

General Info

| | | | |
|--------------------|-------------------------|-----------------|---|
| Product Line | Pass & Seymour | Color | Gray |
| Finish | Matte | UPC Number | 785007189728 |
| Country Of Origin | Mexico | Construction | Plastic |
| Wall Plate Size | Standard Size | Wall Plate Type | Combination, Decorator, Duplex Receptacle |
| Application Sector | Commercial, Residential | Standard | CSA, UL514 |
| Warranty Type | 1-Year Limited Warranty | Type | Wall Plate |

Dimensions

| | | | |
|------------------|---------|------------------|--------|
| Product Width US | 4.56 in | Product Depth US | 0.2 in |
|------------------|---------|------------------|--------|

| | |
|-------------------|--------|
| Product Height US | 4.5 in |
|-------------------|--------|

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|-----------------|-------|
| CSA Listed | Yes | CSA File Number | 17695 |
|------------|-----|-----------------|-------|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|-----------|---------|-----------------|---|
| Thickness | 0.07 in | Number of Gangs | 2 |
|-----------|---------|-----------------|---|

| | | | |
|----------------|--------|---------------|-------------|
| Indoor/Outdoor | Indoor | Mounting Type | Box Mounted |
|----------------|--------|---------------|-------------|

| | |
|-------------|----------|
| Orientation | Vertical |
|-------------|----------|
