

Combination Wall Plate, 1 Duplex Receptacle, 1 Blank and 1 Duplex Receptacle, 3-Gang, 302/304 Stainless Steel



Features & Benefits

- Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness. Brushed finish.
- This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion. Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide. Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes. Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Specifications

General Info

| | | | |
|-------------------|---------------------------------------|--------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Stainless Steel |
| Finish | Metallic | UPC Number | 785007136364 |
| Country Of Origin | United States | Wall Plate Size | Standard Size |
| Wall Plate Type | Blank, Combination, Duplex Receptacle | Application Sector | Commercial, Residential |
| Standard | CSA | Warranty Type | 1-Year Limited Warranty |
| Type | Wall Plate | | |

Dimensions

| | | | |
|-------------------|----------|------------------|--------|
| Product Width US | 6.375 in | Product Depth US | 0.2 in |
| Product Height US | 4.5 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Additional Information

Product Environmental Profile Yes

Technical Information

| | | | |
|----------------|----------|-----------------|---------------|
| Thickness | 0.032 in | Number of Gangs | 3 |
| Indoor/Outdoor | Indoor | Mounting Type | Strap Mounted |
| Orientation | Vertical | | |
