



Ortronics
Clarity TracJack (TJ), Cat 5E, T568A/B, electric ivory
Part No. TJ5E00-13



Clarity 6a, 6 & 5e TracJacks, ETL verified to TIA Category 6a, 6 & 5e component specification. Front-loading and front removable. New universal T568A/B wiring label and tapered wiring towers simplify termination. Center tuned to Clarity patch cords for optimum performance

Features & Benefits

ETL Verified to Category 6A component standard: Ensures standards compliance.

Easy to follow universal wiring label: Quick and user-friendly, eliminates confusion.

Center tuned design: Transparent interface with Clarity 6A/10G cords

Easy lace IDC housing: Reduces wiring time

Standard TracJack footprint: Fits in all TracJack faceplates and housings

Icon compatible, C6A marking on jack face: Supports 606 designation requirements

Specifications

General Info

| | | | |
|--------------------|------------------------|-------------------|---|
| Product Line | Ortronics | Color | Ivory |
| UPC Number | 662875451846 | Country Of Origin | Mexico |
| Application Sector | Commercial, Industrial | Standard | TIA-568.2-D, UL 1863, IEEE 802.3af / 802.3at, 802.3bt Type 3 and Type 4, FCC part 68 Subpart F, IEC-603-7 compliant |
| Warranty Type | 5-Year | Type | Jack |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 0.73 in | Product Depth US | 1.1 in |
| Product Height US | 0.92 in | | |

Additional Information

| | | | |
|----------------|-----|-------------------------------|-----|
| RoHS Compliant | Yes | Product Environmental Profile | Yes |
|----------------|-----|-------------------------------|-----|

Technical Information

| | | | |
|---------------|--------|------------|--------|
| Compatibility | 568A/B | Wire Gauge | 22 AWG |
|---------------|--------|------------|--------|

| | | | |
|-------------------|-----|----------------|-------|
| Termination Style | 110 | Connector Type | RJ-45 |
|-------------------|-----|----------------|-------|

| | |
|-----------|---------|
| Impedance | 100 Ohm |
|-----------|---------|
