



Clarity TracJacks are a front loading solution designed for the workstation. Larger module size provides better visibility and more area to lace and terminate cables.

## Features & Benefits

Easy to follow universal wiring label: Quick, user-friendly, eliminates confusion.

Front removable: Less intrusive access for adds, moves, changes.

Standard TracJack footprint: Fits in all Tracjack faceplates and housings.

Icon compatible, with C6 Marking on jack face: Supports 606 designation requirements.

RoHS compliant: Lead free.

Center tuned design: Transparent interface with Clarity6 cords.

Easy lace IDC housing: Reduces wiring time.

## Specifications

### General Info

Product Line	Ortronics	Color	Ivory
UPC Number	662875480679	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	ANSI/TIA-568-C.2, UL 1863, IEEE 802.3af / 802.3at and Proposed 802.3bt Type 3 and Type 4, FCC part 68 Subpart F, IEC-603-7 compliant
Warranty Type	5-Year	Type	Jack

### Dimensions

Product Width US	0.73 in	Product Depth US	1.1 in
Product Height US	0.92 in		

---

## Additional Information

---

RoHS Compliant      Yes

---

## Technical Information

---

Wire Gauge      22 AWG      Shielded/Unshielded      Unshielded

---

Termination Style      110      Connector Type      RJ-45

---

Performance Level/Tier      Cat 5e      Impedance      100 Ohm

---