



Clarity TracJacks are a front loading solution designed for the workstation. Larger module size provides better visibility and more area to lace and terminate cables.

Features & Benefits

Easy to follow universal wiring label: Quick, user-friendly, eliminates confusion.

Front removable: Less intrusive access for adds, moves, changes.

Standard TracJack footprint: Fits in all Tracjack faceplates and housings.

Icon compatible, with C6 Marking on jack face: Supports 606 designation requirements.

RoHS compliant: Lead free.

Center tuned design: Transparent interface with Clarity6 cords.

Easy lace IDC housing: Reduces wiring time.

Specifications

General Info

Product Line	Ortronics	Color	Black
UPC Number	662875476016	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	UL Standard
Warranty Type	5-Year	Type	Jack

Dimensions

Product Width US	0.73 in	Product Depth US	1.1 in
Product Height US	0.92 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Wire Gauge	22 AWG	Termination Style	110
Connector Type	RJ-45	Impedance	100 Ohm
