




Ortronics
Clarity 6 Shielded TracJack, T568A/B, 180 degree
Part No. TJS600



Clarity 6 Shielded, TracJack, ETL verified to TIA Category 6 component specification. Front-loading and front removable. New universal T568A/B wiring label and tapered wiring towers simplify termination. Center tuned to Clarity 6 Shielded patch cords for optimum performance.

Features & Benefits

C6 and 5E marking on jack face n Backward compatible to shielded Category 3, 5, 5e ETL 3rd party component tested and verified and 6 n Center tuned connectivity design n Co

Easy lace IDC housing accepts larger conductors

Easy to follow universal wiring label—quick and user-friendly

Fits in all TracJack plates and housings

Icon compatible, 6A, C6 and 5E marking on jack face

Center tuned connectivity design

Compatible with 110 impact tool

Specifications

General Info

Product Line	Ortronics	Color	Silver
UPC Number	662875503583	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	UL Standard
Warranty Type	5-Year	Type	Jack

Dimensions

Product Width US	0.73 in	Product Depth US	1.1 in
Product Height US	0.92 in		

Additional Information

RoHS Compliant

Yes

Product Environmental Profile

Yes

Technical Information

Wire Gauge

22 AWG

Termination Style

110

Connector Type

RJ-45

Impedance

100 Ohm
