



radiant Collection  
**radiant® 15A 3-Way Switch, North American Compliant, Black**  
Part No. TM873NABK



Allowing control of a light or fixture from two separately located switches, the radiant® 3-Way Switch upgrades your space with clean lines and smooth paddle action for a sophisticated touch. As a North American Compliant device, this switch is ideal for use in projects subject to the Buy America Act. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

For use with incandescent lights/bulbs only.

Uses a paddle switch for smoother control with a low-profile aesthetic.

Designed to install easily with a narrower back body and captivated mounting screws.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Replaces any standard switch with ease, in as little as 10 minutes.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

North American devices are ideal for use on projects subject to the provisions of the Buy America Act.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007007992
Country Of Origin	Mexico	Switch Type	Paddle
Number of Switches	1	Application Sector	Commercial, Residential
Warranty Type	1-Year Limited Warranty		

### Dimensions

---

Product Width US	1.43 in	Product Depth US	1.27 in
------------------	---------	------------------	---------

---

Product Height US	4.19 in
-------------------	---------

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

### Technical Information

---

Contact Rating	15 Amp, 120/125 VAC	Number of Gangs	1
----------------	---------------------	-----------------	---

---

Amperage	15 A	Number of Poles	3-Way, Single Pole
----------	------	-----------------	--------------------

---

Wire Size	#14 - #10 AWG	Mounting Type	Box
-----------	---------------	---------------	-----

---