



Pass and Seymour  
**Discontinued - Tamper-Resistant Single Receptacle with 3.1A USB Charger, Black**  
Part No. TM88USBBKCC6



Charge more devices with less clutter. Legrand's full line of charging solutions is designed to power up mobile devices quickly and reliably without the need for bulky AC adapters.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

## Features & Benefits

|  |   |
|--|---|
| Classic duplex style matches traditional devices like 3232s              | 2 USB A-Type charging ports 3.1A total charging capacity (simultaneously charges 2 tablets) |
| Compatible with USB 2.0 & 3.0 devices                                    | Efficient 5Vdc transformer  |
| Side and back-wire terminals   | Tamper-Resistant receptacle to meet latest NEC: code requirements                           |
| Self-grounding clip standard on all Commercial and Hospital Grade models | Slim 1.3-inch depth   |
| cULus listed   |   |

## Specifications

### General Info

|              |                |                   |       |
|--------------|----------------|-------------------|-------|
| Product Line | Pass & Seymour | Color             | Black |
| UPC Number   | 785007032192   | Country Of Origin | China |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

### Technical Information

|                     |      |              |       |
|---------------------|------|--------------|-------|
| Is Tamper-Resistant | Yes  | USB Amperage | 3.1 A |
| USB Power Output    | 15 W | Amperage     | 15 A  |