



Trademaster Plate 2-Gang 1toggle 1 Blank

Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	UPC Number	785007275261
Country Of Origin	Mexico	Wall Plate Type	Blank, Combination, Toggle Switch
Application Sector	Commercial, Residential	Standard	CSA, UL514
Warranty Type	Limited Lifetime Warranty	Type	Wall Plate

Dimensions

Product Width US	4.75 in	Product Depth US	0.25 in
Product Height US	4.6875 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Cutout	Toggle and Blank	Thickness	0.07 in
--------	------------------	-----------	---------

Number of Gangs	2	Indoor/Outdoor	Indoor
-----------------	---	----------------	--------

Mounting Type	Exposed Screws	Orientation	Horizontal
---------------	----------------	-------------	------------
