Pass and Seymour

Blank Plates, Box Mounted, One Gang, Light Almond

Part No. TP13LA



The Trademaster 1-gang blank wall plate is constructed from high-impact, injection molded nylon plastic. Oversized in height and width by 3/16^{ths} of an inch, this plate could completely cover an opening in a wall that a standard plate fails to conceal.

Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Wall Plate Type	Blank	Application Sector	Residential/Commercial
Standard	CSA, UL514		

Dimensions

Product Width US	2.9375 in	Product Depth US	0.25 in
Product Height US	4.6875 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes

CSA File Number	C22.2 No. 42- C22.2 No. 223

Additional Information

RoHS Conformant	Yes	Product Environmental Profile	Yes

Technical Information

Cutout	Blank	Thickness	0.07 in
Number of Gangs	1	Mounting Type	Exposed Screws