



Pass and Seymour  
TradeMaster® 1-Gang Nylon Wall Plate, Blank, Box Mounted, Light Almond  
Part No. TP13LA



The Trademaster 1-gang blank wall plate is constructed from high-impact, injection molded nylon plastic. Oversized in height and width by 3/16<sup>ths</sup> of an inch, this plate could completely cover an opening in a wall that a standard plate fails to conceal.

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007274745
Country Of Origin	United States	Construction	Plastic
Wall Plate Size	Standard Size	Wall Plate Type	Blank
Application Sector	Commercial, Residential	Standard	CSA, UL514
Warranty Type	1-Year Limited Warranty	Type	Wall Plate

### Dimensions

Product Width US	2.9375 in	Product Depth US	0.25 in
------------------	-----------	------------------	---------

---

Product Height US 4.6875 in

---

### Listing Agencies / 3rd Party Agencies

---

CSA Listed Yes cULus Listed Yes

---

CSA File Number C22.2 No. 42- C22.2 No. 223

---

### Additional Information

---

RoHS Compliant Yes Product Environmental Profile Yes

---

### Technical Information

---

Thickness 0.07 in Number of Gangs 1

---

Indoor/Outdoor Indoor Mounting Type Box Mounted

---

Orientation Vertical

---