



Pass and Seymour  
TradeMaster® 1-Gang Nylon Wall Plate, 2.156-in Power Outlet Receptacle Opening, 2 Mtg Holes, Brown  
Part No. TP724

OneGang Power Outlet Receptacle Opening, 2.156 hole for 2.125 diameter device -2 mtg. holes, White Nylon.



## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.) Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond. Preferred for hospital, industrial, institutional, and other high-abuse applications.

Nominal thickness, .070 inch.

## Specifications

### General Info

|                    |                         |                 |               |
|--------------------|-------------------------|-----------------|---------------|
| Product Line       | Pass & Seymour          | Color           | Brown         |
| Finish             | Matte                   | UPC Number      | 785007275926  |
| Country Of Origin  | Mexico                  | Construction    | Plastic       |
| Wall Plate Size    | Standard Size           | Wall Plate Type | Outlet, Round |
| Application Sector | Commercial, Residential | Standard        | CSA, UL514    |
| Warranty Type      | 1-Year Limited Warranty | Type            | Wall Plate    |

### Dimensions

|                   |           |                          |          |
|-------------------|-----------|--------------------------|----------|
| Product Width US  | 2.9375 in | Product Depth US         | 0.25 in  |
| Product Height US | 4.6875 in | Circular Outlet Diameter | 2.156 mm |

---

## Listing Agencies / 3rd Party Agencies

---

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 143222 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

---

## Additional Information

---

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

---

## Technical Information

---

|                |          |                 |               |
|----------------|----------|-----------------|---------------|
| Thickness      | 0.07 in  | Number of Gangs | 1             |
| Indoor/Outdoor | Indoor   | Mounting Type   | Strap Mounted |
| Orientation    | Vertical |                 |               |

---