Pass and Seymour

Hard-Use Spec Grade Plug Load Controllable Receptacle, 15A, 125V, White

Part No. TR5262CDW



Permanent controlled receptacle marking allows for long-lasting, easy identification of controlled receptacle for end-users. NEMA-approved and compliant with NEC, CA Title 24, and ASHRAE Energy Efficiency Standard 90.1.

Features & Benefits

Can be wired to any number of system-based or stand-alone plug load control solutions.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.

Dual mechanical shutter system to help prevent insertion of foreign objects (for Tamper-Resistant models).

CH Version Only: Split circuit tab broken at the factory, allowing half of the receptacle to be controlled.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly.

Permanent controlled receptacle markings using abrasion resistant ink.

Tri-drive brass-plated terminal screws. Two back-wire holes for more wiring flexibility.

Strap tabs wrap around face to prevent strap from separating from face and back body.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.63 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes

Technical Information

Amperage	15 A