




Pass and Seymour
20A 125V Hard Use Spec-Grade Tamper-Resistant Half-Controlled Plug Load Duplex Receptacle, Ivory
Part No. TR5362CHI



Permanent controlled receptacle marking allows for long-lasting, easy identification of controlled receptacle for end-users. NEMA-approved and compliant with NEC, CA Title 24, and ASHRAE Energy Efficiency Standard 90.1.

Features & Benefits

- Can be wired to any number of system-based or stand-alone plug load control solutions.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.
- Strap tabs wrap around face to prevent strap from separating from face and back body.
- For covering patents, see www.legrand.us/patents.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Permanent controlled receptacle markings using abrasion resistant ink.
- Tri-drive brass-plated terminal screws. Two back-wire holes for more wiring flexibility.
- CH Version Only: Split circuit tab broken at the factory, allowing half of the receptacle to be controlled.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007051155	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Energy Saving On/Off, Tamper-Resistant
Application Sector	Commercial	Standard	FEDSPEC
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	1.13 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Indoor/Outdoor	Indoor
----------------	--------
