



Tamper-Resistant Isolated Ground Decorator Hospital Grade Duplex Receptacle, Back and Side Wire, 20amp 125volt, White. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

IG symbol and Isolated Ground markings for easy identification and circuit delineation.

High-impact resistant nylon face resists impacts and scrapes.

Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Side and internal screw-pressure-plate back wire capability with #14 - #10 AWG copper or copper-clad, solid or stranded wire.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Triple-wipe brass contacts ensure lasting, positive contact with plug blades.

Corrosion-resistant plated steel strap.

Plastic barrier isolates grounding terminal from mounting strap and metal boxes.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|----------------------|
| Product Line | Pass & Seymour | Color | Ivory |
| UPC Number | 785007012354 | Country Of Origin | Mexico |
| Application Sector | Commercial | Standard | cULus UL498, FEDSPEC |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 1.187 in | Product Depth US | 1.25 in |
| Product Height US | 3.625 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|---------------------|--------------------------|---------------------|-----|
| Dielectric Strength | Withstands 2000V minimum | Is Tamper-Resistant | Yes |
|---------------------|--------------------------|---------------------|-----|

| | | | |
|------------|--------------------|-----------------|---|
| Connection | Back and side wire | Number of Wires | 3 |
|------------|--------------------|-----------------|---|

| | | | |
|--------------------|--------------|----------|------|
| Temperature Rating | -40° - 60° C | Amperage | 20 A |
|--------------------|--------------|----------|------|

| | | | |
|-----------------|-------------|-----------|-------------|
| Number of Poles | Double Pole | Wire Size | 14 - 10 AWG |
|-----------------|-------------|-----------|-------------|

| | | | |
|--------------------------|-----------------------|--|--|
| Environmental Conditions | Flammability: UL94 V2 | | |
|--------------------------|-----------------------|--|--|
