



Pass and Seymour
Toggle Slide Dimmer Low Voltage Single Pole/3-Way, 700VA, TRI
Part No. TSDLV703PTC



700 VA, Preset, Single Pole/3-Way Toggle Slide Dimmer

Features & Benefits

Matches appearance of standard Pass & Seymour toggle switch

Interchangeable face covers are available in seven different colors

Lifetime warranty

All models are Single Pole/3-Way capable

Highest wattage rating

Specifications

General Info

| | | | |
|--------------------|--|--------------------|-----------------------------------|
| Product Line | Pass & Seymour | Color | Ivory, Light Almond, White |
| Finish | Gloss | UPC Number | 785007216165 |
| Country Of Origin | China | Product Series | Trademaster |
| Features | Color Change Kit, Low-End Trim (Dim Range) | Switch Type | Single Pole 3-Way, Slider, Toggle |
| Number of Switches | 1 | Application Sector | Residential |
| Warranty Type | Limited Lifetime Warranty | | |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 2.5 in | Product Depth US | 1.4 in |
| Product Height US | 4.19 in | | |

Technical Information

| | | | |
|-----------------------|-------------------|----------------------|--|
| Preset | Yes | Load Rating | 120V 700VA (MLV - Halogen), 120V 700VA (MLV - Incandescent) |
| Dimming Compatibility | Forward Phase | Frequency Rating | 60 Hz |
| Number of Poles | Single Pole 3-Way | Wire Size | #14 - #10 AWG |
| Requires Neutral Wire | No | Indoor/Outdoor | Indoor |
| Mounting Type | Wall Box | Wire Connection Type | Screw Terminals |
| Voltage | 120 VAC | Load Type | Halogen, Incandescent |
