



**Wiremold**  
**Plug-In Outlet Center Unit / 120V/15A/24 long/8 O/L /lighted switch/15' cord**  
Part No. UL300BD



Eight outlets, lighted switch, rugged gray aluminum housing, 15A, 15' (4.6m) 14/3 SJT black cord with NEMA5-15 plug. Length 24" (609mm). Receptacle center-to-center 2" (51mm). Snap-on, slide-off mounting.

## Features & Benefits

Eight outlets, lighted switch, rugged gray aluminum housing, 15A, 6' (1.8m) 14/3 SJT black cord with NEMA5-15 plug. Length 24" (609mm). Receptacle center-to-center 2" (51mm). Snap-on, slide-off mounting.

## Specifications

### General Info

|                       |                                                       |                    |              |
|-----------------------|-------------------------------------------------------|--------------------|--------------|
| Product Line          | Wiremold                                              | UPC Number         | 786776043013 |
| Country Of Origin     | Mexico                                                | Receptacle Type    | Simplex      |
| Number of Receptacles | 8                                                     | Application Sector | Commercial   |
| Standard              | cULus Recognized: File E66421 Guide<br>XBYS XUHT VZCA | Type               | PIOC         |

### Dimensions

|                   |         |                   |         |
|-------------------|---------|-------------------|---------|
| Product Width US  | 2.0 in  | Product Weight US | 3.25 lb |
| Product Length US | 24.0 in |                   |         |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E66421 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Trade Programs

---

|       |     |
|-------|-----|
| USMCA | Yes |
|-------|-----|

---

### Additional Information

---

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

---

### Technical Information

---

|                |          |                          |                        |
|----------------|----------|--------------------------|------------------------|
| Phase          | Single   | Amperage                 | 15 A                   |
| Enclosure Type | Aluminum | Mounting Type            | Slide-off, Snap-on     |
| Voltage        | 125.0 V  | Environmental Conditions | Dry interior locations |

---