



Wattstopper
Ultrasonic Ceiling Occupancy Sensor, 24 VDC, 500 sq ft, USA
Part No. UT-300-1-U



Wattstopper's UT-300 Ultrasonic Ceiling Sensors automatically turn lighting on and off based on occupancy. The sensors mount on the ceiling with a flat, unobtrusive appearance and provides 360° coverage.

Features & Benefits

Architecturally appealing low-profile appearance

Accepts low-voltage switch input for manual-on operation

Walk-through mode increases savings potential

Ultrasonic diffusers give more comprehensive coverage

Plug terminal wiring for quick and easy installation

Automatic or manual-on operation when used with a BZ-150 Power Pack

Specifications

General Info

Product Line	Wattstopper	Replaced by Part Number	DT-300-U, UT-300-1
Color	White	Finish	Glossy
UPC Number	754182928866	Country Of Origin	United States
Product Series	UT-300	Features	Adjustable Time Delay, Indicator Lights, Isolated Relay, Light Level Sensor, Power Pack Required, Sensitivity Adjustment
Installation Location	Ceiling	Included	Mounting Screws
Application Sector	Commercial	Standard	UL, cUL, PEP, BAA, TAA
Warranty Type	5-Year	Type	Sensor

Dimensions

Product Width US	4.5 in	Product Weight US	0.2 lb
------------------	--------	-------------------	--------

Product Volume US	44.4 cu in	Product Depth US	1.5 in
-------------------	------------	------------------	--------

Product Height US	4.5 in		
-------------------	--------	--	--

Additional Information

Product Environmental Profile	Yes		
-------------------------------	-----	--	--

Technical Information

Operating Temperature Min	32 °F	Timer Type	DIP Switch
---------------------------	-------	------------	------------

Compatibility	BZ Power Packs	Ultrasonic Frequency	40 kHz
---------------	----------------	----------------------	--------

Has Battery	No	Sensor Coverage Pattern	360 deg
-------------	----	-------------------------	---------

Sensor Type	Occupancy	Operating Temperature Max	131 °F
-------------	-----------	---------------------------	--------

Sensor Mounting Height	8-10 ft	Number of Buttons	0
------------------------	---------	-------------------	---

Number of Rockers	0	Sensor Technology	Ultrasonic
-------------------	---	-------------------	------------

Timer Duration	30 Seconds, 5-30 Minutes	Indicator	Ultrasonic Detection LED
----------------	--------------------------	-----------	--------------------------

Input Voltage	24 VDC/VAC	Indoor/Outdoor	Indoor
---------------	------------	----------------	--------

Sensor Coverage	500 sq ft	Mounting Type	4 in Octagonal J-Box, Ceiling Tile, Surface
-----------------	-----------	---------------	--

On Function	Auto On	Current Draw	25 mA
-------------	---------	--------------	-------

Operating Temperature	0°-55°C, 32°-131°F	Operating Humidity	5-95% RH (Non- Condensing)
-----------------------	--------------------	--------------------	-------------------------------

Sensing Range	24 x 24 ft	Wire Connection Type	Terminal Block
---------------	------------	----------------------	----------------

Engraving Type	Blank	Storage Temperature	23° - 176° F, -5° - 80° C
----------------	-------	---------------------	---------------------------
