



Extra Heavy-Duty While-In-Use Weatherproof Cover, 2 Gang



## Features & Benefits

Comply with NEC 2014 Section 406.9 (B)(1) for wet location covers, and conforms to NEMA 3R.

Covers are self closing as required by UL514C42.3.

Body, cover, and plates are made of robust polycarbonate for added durability.

Single receptacle plate available in 1.405 inch and 1.595 inch openings.

Shallow covers accommodate up to 14/3 AWG extension cords.

Listed and identified as : Extra Duty: .

Covers mount vertically and horizontally.

Mounting screws made of 302 stainless steel for corrosion resistance.

Deep model available for 20A locking plugs.

New trigger latch opens easily with one finger.

## Specifications

### General Info

|                 |                         |                    |                         |
|-----------------|-------------------------|--------------------|-------------------------|
| Product Line    | Pass & Seymour          | Color              | Clear                   |
| UPC Number      | 785007320947            | Country Of Origin  | United States           |
| Wall Plate Type | Custom                  | Application Sector | Commercial, Residential |
| Warranty Type   | 1-Year Limited Warranty | Type               | Wall Plate Accessories  |

### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

### Technical Information

Number of Gangs 2 Indoor/Outdoor Indoor

---

Number of Outlets      2

---