



Pass and Seymour  
4-in Round Outdoor Cluster Cover, Gray  
Part No. WPRB11

Weatherproof 4-inch Round Outdoor Cluster Cover, Blank 1 Hole  
1/2-in With Gasket and Screws



## Features & Benefits

Wide range of rectangular and round covers.

Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.

Kits available combining fixtures, lamp covers, and accessories.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007117066
Country Of Origin	India	Features	Weatherproof
Wall Plate Type	Custom	Application Sector	Industrial
Standard	UL listed	Warranty Type	1-Year Limited Warranty
Type	Weatherproof Cover		

### Dimensions

Product Width US	4.625 in	Product Depth US	1.0 in
Product Height US	4.625 in		

### Listing Agencies / 3rd Party Agencies

---

CSA Listed

Yes

CSA File Number

17695

---

**Technical Information**

---

Indoor/Outdoor

Indoor

Mounting Type

Box Mounted

---

Number of Outlets

1

---