



Pass and Seymour
Wide Slide Fan Speed Control De-hummer, Single Pole, Tri-Color
Part No. WSDH16TC



1.6 AMP Wide Slide Dehummer Fan Control

Features & Benefits

- 4 Speed fan control with easy : slide to off" operation
- De-hummer feature virtually eliminates fan motor : hum" for quiet fan speed control
- Constant memory returns lights to previous level after a power failure
- 1.6A Rating single pole operation
- Supports other colors with WSKIT** interchangeable face plates

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory, Light Almond, White
Finish	Matte	UPC Number	785007053579
Country Of Origin	China	Application Sector	Residential
Standard	CSA Listed, cULus, UL Listed		

Dimensions

Product Width US	1.75 in	Product Depth US	1.25 in
Product Height US	4.25 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Connection	Back Wired	Contact Rating	120VAC
Amperage	1.6 A	Number of Poles	Single Pole
Wire Size	#14 - #10 AWG	Speed Range	Variable
Environmental Conditions	Indoor Only		
