



Wiremold
Exterior Box Cover Assembly, 2 NEMA 5-20R Locking Receptacles, Brown (COVER ONLY)
Part No. XB814C520BN



The brown Outdoor Ground Box cover assembly is prewired on a single circuit with (2) 20A weather resistant duplex receptacles. **CAUTION:** All ground box electrical circuits must be protected by a Ground Fault Circuit Interrupter upstream from the ground box. **NOTE:** Cover must be closed while in use. Use only molded plug and cord assemblies that are rated for outdoor use. **NOTE:** Maximum length of plug allowed at end of cord is 3" (76mm).

Features & Benefits

- cUL Coming Soon
- UL listed to UL50E Type 6P (NEMA 6P) and IP68 requirements while in use
- ADA compliant
- Outdoor-rated construction
- Keeps receptacles and connections dry even when submerged

Specifications

General Info

Product Line	Wiremold	UPC Number	786776187199
Country Of Origin	China	Construction	Assembled
Number of Knockouts	1	Application Sector	Commercial
Standard	UL Listed Outdoor In-Ground Boxes: File E486738 Guide QCNL.	Type	Cover

Dimensions

Product Width US	7.375 in	Product Weight US	9.0 lb
Product Height US	19.625 in	Product Length US	14.0 in
Cubic Capacity	123 in ³		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E486738	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Number of Outlets 4
