legrand®

Cablofil

FTFB90

HORIZONTAL 90° ELBOW BASE

FEATURES

- Strong corrosion resistant steel construction
- Rolled edge for cable protection
- Unique design allows covers to snap on
- 18 gage steel

COMPATIBLE COVER

FTCFB90

(sold separately)



	TRAY HEIGHT		TRAY WIDTH (W)		RADIUS (R)		LENGTH 1 (L1)		LENGTH 2 (L2)		TANGENT (C)		WEIGHT		PG	BL
	INCHES	MM	INCHES	MM	INCHES	MM	INCHES	MM	INCHES	MM	INCHES	MM	LBS	KG	STANDARD	
FTFB90 50/50	2.0	50	2.0	50	0.8	20	-	-	3.9	100	1.2	30	0.6	0,26	340 914	960 022
FTFB90 50/100	2.0	50	3.9	100	3.9	100	9.1	230	9.1	230	1.2	30	1.6	0,74	340 915	960 023
FTFB90 50/200	2.0	50	7.9	200	3.9	100	13.0	330	13.0	330	1.2	30	3.7	1,67	340 917	960 024
FTFB90 50/300	2.0	50	11.8	300	3.9	100	16.9	430	16.9	430	1.2	30	6.5	2,94	340 918	960 025
FTFB90 100/100	3.9	100	3.9	100	3.9	100	9.1	230	9.1	230	1.2	30	2.1	0,97	340 930	960 026
FTFB90 100/200	3.9	100	7.8	200	3.9	100	13.0	330	13.0	330	1.2	30	4.5	2,03	340 932	960 027
FTFB90 100/300	3.9	100	11.8	300	3.9	100	16.9	430	16.9	430	1.2	30	7.3	3,29	340 933	960 028
FTFB90 100/500	3.9	100	19.7	500	5.9	150	27.6	700	27.6	700	2.0	50	17.9	8,14	340 935	960 029
FTFB90 100/600	3.9	100	23.6	600	5.9	150	31.5	800	31.5	800	2.0	50	22.5	10,20	341 936	960 030

FINISHES			
SYMBOL		MATERIAL	FINISH & STANDARD
STANDARD	PG	Carbon Steel	**Pre-Galvanized:** Continuous Galvanization Before Fabrication ASTM A 653
STANDARD	BL	Carbon Steel ASTM A510 Grade 1008	**Black Painted:** Black Powder Coated ASTM D 3451

© 2012 Legrand/Cablofil 02/1

Legrand/Cablofil
8319 State Route 4
Mascoutah, IL 62258 USA
1-800-658-4641
618-566-3230
Fax 618-566-3250
www.legrand.us/cablofil