Pass and Seymour

60A 220/208V 18-60R Straight Blade Single Flush Receptacle, 4-Pole, 4-Wire

Part No. 3870

Straight Blade Receptacle 60A 120/208V

Features & Benefits

Quality Materials.

Durability.

Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Application Sector	Industrial	Standard	UL 498

Dimensions

Product Width US	2.5 in	Product Depth US	2.2 in
Product Height US	3.75 in		

Technical Information

Phase	4	Number of Wires	4
Amperage	60 A	Number of Poles	4-Way
Wire Size	8 - 4 AWG	Voltage	120.0 V