Pass and Seymour

Discontinued - Non-Grounding Single-Pole Combination Switch and Pilot Light, Ivory | Sub 692IG

Part No. 692I

Single Pole, Single Pilot Light, Combination Switch, 15 amps, 120/125 volts, Ivory.

Features & Benefits

- Easily accessible break-off separate or common feed.
- Side wire #12 and #14 AWG.
- Grounding combination devices meet NEC Requirements.
- For covering patents, see www.legrand.us/patents.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Two devices fit into the space of one.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	692IG
Color	Ivory	UPC Number	785007692013
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL20	Type	Combination

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes

Technical Information

Contact Configuration	N-O	Operating Cycles	30000
Actuator	Toggle	Connection	non-grounding, Side wire
Contact Rating	15 Amp, 120/125 VAC	Amperage	15 A
Number of Poles	Single Pole	Environmental Conditions	Flammability: UL94 V2