Wiremold

CabinetMate Plug-In Outlet Center Unit / 120V/20A / 77" long / 12 O/L / 6' cord / Computer Grade Surge

Part No. 7712BCS20R



Twelve outlets with t-slots. 6' (1.8m) cord. Length 77"" (2m). 20A resettable circiut breaker. Computer grade surge protection, 20 Amps.

Features & Benefits

Twelve outlets with t-slots. 6' (1.8m) cord. Length 77" (2m). 20A resettable circiut breaker. Computer grade surge protection, 20 Amps.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776052718
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA	Type	PIOC

Dimensions

Product Width US	77.0 in	Product Height US	1.19 in
Product Length US	1.5 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes

Buy American Act Compliance

NAFTA	Yes

Additional Information

RoHS Conformant	Yes

Technical Information

Phase	Single Stage	Frequency Rating	+35dB Hz
Connection	Cord-ended	Class	75
Amperage	20 A	Short Circuit Rating	36000 Amps [12000 Amps L-N 12000 Amps L-G 12000 Amps N-G]
Response Time	<1 ns	Mounting Type	Spring Clip
Mounting	Yes	Type of Indicators	Light
Voltage	600.0 V		